

# NH slimline fuse-switch disconnectors, size 00 to 3



Busbar system Page 12 Component adaptors Page 14

## Material:

- Polyamide (PA 6.6)
- Fire protection corresponding to UL 94-V0
- Contact tracks: Partially silver-plated hard copper

## Colour:

- Chassis: RAL 7035
- Cover: RAL 7001
- Handle: RAL 7016

## Basis of test:

- IEC 60 947-3
- IEC 60 269-2 (fuse inserts)

## Note:

- When using NH slimline fuse-switch disconnectors on busbars with contact hazard protection cover, the contact terminal must be used

## Size 00 to 3, with electronic fuse monitoring

Size	Packs of	00	1	2	3	Page
Version		3-pole, switchable	3-pole, switchable	3-pole, switchable	3-pole, switchable	
Rated current max. A		160	250	400	630	
Rated operating voltage V, ~		690, 3~	690, 3~	690, 3~	690, 3~	
Number of poles		3-pole	3-pole	3-pole	3-pole	
Cable outlet		Top/bottom	Top/bottom	Top/bottom	Top/bottom	
Type of connection		Screw M8	Bolt M12	Bolt M12	Bolt M12	
Connection of round conductors mm <sup>2</sup>		2.5 - 95	6 - 240	6 - 240	6 - 240	
For converter installation		■	■	■	■	
For bar systems with centre-to-centre spacing mm		185	185	185	185	
For bar thickness mm		10	10	10	10	
<b>Model No.</b>	1 pc(s).	<b>9677.015</b>	<b>9677.115</b>	<b>9677.215</b>	<b>9677.315</b>	
<b>Accessories</b>						
Connection space cover	1 pc(s).	see page	9677.410	9677.410	9677.410	22
Contact terminals	3 pc(s).	9677.450	9677.460	9677.460	9677.460	22
Busbar terminal	3 pc(s).	9677.470	9677.480	9677.480	9677.480	22
Micro-switch	5 pc(s).	3071.000	3071.000	3071.000	3071.000	Cat. 34, 263
Prism terminal	3 pc(s).	-	-	-	-	23
V connection terminals	3 pc(s).	-	9677.430	9677.430	9677.440	23