

# TopTherm roof-mounted fans



Climate control accessories Page 369 Vent attachment TS Page 383

The active roof-mounted fans fit precisely onto the cut-outs of the small and medium performance categories of TopTherm roof-mounted cooling units.

**Material:**  
– Sheet steel, spray-finished

**Colour:**  
– RAL 7035

**Protection category IP to IEC 60 529:**  
– IP 43

**Technical details:**  
Available on the Internet

**Supply includes:**  
– Unit ready for connection with built-in radial fan  
– Sealing and assembly parts

## Air throughput 400 – 800 m<sup>3</sup>/h

Model No.	Packs of	3149.410	3149.420	3149.440	3149.810	3149.820	3149.840	Page
Rated operating voltage V, ~, Hz		115, 1~, 50/60	230, 1~, 50/60	400, 3~, 50/60 460, 3~, 60	115, 1~, 50/60	230, 1~, 50/60	400, 3~, 50/60 460, 3~, 60	
<b>Air throughput, unimpeded air flow m<sup>3</sup>/h</b>		<b>400</b>	<b>400</b>	<b>400</b>	<b>800</b>	<b>800</b>	<b>800</b>	
Rated current A		1.1 / 1.6	0.55 / 0.88	0.35 / 0.35	1.5 / 2.2	0.75 / 1.1	0.35 / 0.55	
Power consumption W		120 / 170	120 / 170	95 / 140	170 / 225	170 / 225	180 / 310	
Width mm		550	550	550	550	550	550	
Height mm		125	125	125	125	125	125	
Depth mm		370	370	370	370	370	370	
Required mounting cut-out mm		475 x 260	475 x 260	475 x 260	475 x 260	475 x 260	475 x 260	
Operating temperature range		-10°C...+55°C	-10°C...+55°C	-10°C...+55°C	-10°C...+55°C	-10°C...+55°C	-10°C...+55°C	
Noise level dB(A)		68 / 69	68 / 69	68 / 69	69 / 70	69 / 70	69 / 70	
Weight kg		10.0	10.0	10.0	11.0	11.0	11.0	
<b>Accessories</b>								
Roof plates TS	1 pc(s).	8801.320	8801.320	8801.320	8801.320	8801.320	8801.320	383
Digital enclosure internal temperature display and thermostat	1 pc(s).	3114.200	3114.200	–	3114.200	3114.200	–	379
Speed control	1 pc(s).	3120.200	3120.200	–	3120.200	3120.200	–	381
Enclosure internal thermostat	1 pc(s).	3110.000	3110.000	–	3110.000	3110.000	–	379