

Air/water heat exchangers



Climate control accessories Page 369 Chillers Page 361 Therm software Page 385

Colour:

– RAL 7035

Protection category IP to IEC 60 529:

– IP 55

Cooling medium:

– Water (see Internet for specifications)

Supply includes:

- Fully wired ready for connection (plug-in terminal strip)
- Drilling template
- Sealing and assembly parts

Note:

- Use 3-pole miniature circuit-breaker

Approvals:

Available on the Internet

Performance diagrams:

Available on the Internet

Technical details:

Available on the Internet

Output class 7000 W, wall-mounted

Model No.		Packs of	3216.480	Page
Water-carrying parts	Copper/brass (Cu/CuZn)		■	
Temperature control	Thermostat-controlled magnetic valve		■	
Total cooling output L35 W10, 500 l/h kW			7	
Total cooling output L35 W20, 500 l/h kW			4.5	
Rated operating voltage V, ~, Hz			400, 3~, 50 460, 3~, 60	
Width mm			450	
Height mm			1800	
Depth mm			300	
Rated current max. A			1.4 / 1.6	
Pre-fuse A			4	
Operating temperature range			+1°C...+70°C	
Setting range			+20°C...+55°C	
Water inlet temperature			+1°C...+30°C	
Permissible operating pressure (p. max.) bar			1 - 10	
Air throughput of fans (unimpeded air flow) m³/h			3630 / 4670	
Weight kg			79.0	
Accessories				
Door-operated switch	1 pc(s).		4127.010	639
Condensate hose	1 pc(s).		3301.612	377
Flow regulator valve			see page	378