

Wall-mounted enclosures AE



System accessories Page 507 **Socket strips** Page 422 **Cage nuts** Page 624 **Glazed doors** Page 556

Wall-mounted enclosure for small networks with a high protection category.

Material:

- Enclosure: Sheet steel

Surface finish:

- Enclosure: Powder-coated
- Mounting angles: Zinc-plated

Colour:

- RAL 7035

Protection category IP to IEC 60 529:

- Up to IP 66 (depending on the selected gland pate)

Supply includes:

- Enclosure with hinged door
- Door hinged on the right, may be swapped to the left
- Cam lock with 3 mm double-bit insert
- Gland plate with brush strip for cable entry in the enclosure base
- Mounting angles, 482.6 mm (19"), fully depth adjustable
- C rail, for cable clamping on the rear panel
- Metal bracket for optional accommodation of an earth rail or 482.6 mm (19") socket strip

Approvals:

- UL
- CSA
- TÜV
- Germanischer Lloyd
- Lloyds Register of Shipping
- VDE

Technical details:

Available on the Internet

with 482.6 mm (19") mounting angles, depth-variable

| Units U | Packs of | 8 | 13 | 16 | Page |
|--|----------|-----------------|-----------------|-----------------|------|
| Width mm | | 600 | 600 | 600 | |
| Height mm | | 380 | 600 | 760 | |
| Depth mm | | 350 | 350 | 350 | |
| Max. installation depth mm | | 310 | 310 | 310 | |
| Cam locks | | 1 | 2 | 2 | |
| Model No. | 1 pc(s). | 7641.000 | 7643.000 | 7645.000 | |
| Gland plate, size | | 5 | 5 | 5 | |
| Gland plates, qty. | | 1 | 1 | 1 | |
| Accessories | | | | | |
| Wall mounting bracket | | see page | see page | see page | 587 |
| Viewing window | | see page | see page | see page | 556 |
| Component shelf 2 U, static installation | 1 pc(s). | 7119.250 | 7119.250 | 7119.250 | 631 |
| Earth rail, horizontal | 1 pc(s). | 7113.000 | 7113.000 | 7113.000 | 646 |
| Lock systems | | from page | from page | from page | 560 |