

482.6 mm (19") installation system

Mounting angles



Additional fastening attachment for mounting angles

for 800 mm wide network enclosures

For upgrading existing DK-TS applications. The additional fastening attachment counteracts bending of the mounting angles mounted on installation brackets in case of unevenly distributed loads. It is attached directly to 482.6 mm (19") mounting angles and to the punched section with mounting flange fitted in the depth (inner mounting level).

Material:

- Sheet steel

Supply includes:

- Assembly parts

Packs of	Model No.
2 pc(s).	7284.135



Also required:

- TS punched section with mounting flange, for the inner mounting level, see page 606 – 607



Mounting angles, 482.6 mm (19")

for FlatBox

L-shaped bracket as 2nd mounting level.

Material:

- Sheet steel

Supply includes:

- Assembly parts for fast, toolless assembly

Note:

- The 2nd attachment level should always be ordered in the same height as the basic enclosure
- Partial configuration is not possible

U	Packs of	Model No.
6	2 pc(s).	7507.706
9	2 pc(s).	7507.709
12	2 pc(s).	7507.712
15	2 pc(s).	7507.715
18	2 pc(s).	7507.718
21	2 pc(s).	7507.721



Adhesive measurement strip, 482.6 mm (19")

For upgrading existing DK-TS applications.

Made from robust aluminium foil, guarantees easy handling and durability. With numerical labelling on a 482.6 mm (19") pitch pattern for clear identification of the various height units. The double-sided labelling allows the counting direction to be freely selected, up to a maximum of 56 U. In this way, clear documentation of the various mounting parts is easily achieved.

Material:

- Aluminium foil

U labelling range	Packs of	Model No.
1 – 56	1 pc(s).	7950.100