



Side panel, plug-type

for TS

Side panel, lockable with 2 options:

- With lock
- Internal latch

Plug-&-play compatibility system – Insert side panel into the base, press upwards and rotate the two toggle locks – there is no faster way of finishing off an entire enclosure suite at the side.

Material:

Sheet steel, powder-coated

Colour:

RAL 7035/RAL 9005

Protection category:

IP 20/NEMA 1

Supply includes:

2 side panels with toggle locks.

Note:

These side panels must be notched centrally in conjunction with punched sections with mounting flange for the external level.



For enclosures		Model No. DK	
Height mm	Depth mm	RAL 7035	RAL 9005
800	600	7824.086	–
1000	600	7824.106	–
1200	600	7824.126	–
1200	800	7824.128	–
1200	900	7824.129	7816.129
1200	1000	7824.120	7816.120
1400	600	7824.146¹⁾	–
1400	800	7824.148	–
1600	600	7824.166	–
1600	800	7824.168	–
1800	600	7824.186	–
1800	800	7824.188	–
1800	900	7824.189	–
1800	1000	7824.180¹⁾	–
2000	600	7824.206	–
2000	800	7824.208	–
2000	900	7824.209	7816.209
2000	1000	7824.200	7816.200¹⁾
2200	600	7824.226	–
2200	800	7824.228	–
2200	900	7824.229	7816.229¹⁾
2200	1000	7824.220	7816.220¹⁾

¹⁾ Delivery times available on request.

Accessories:

TS punched section with mounting flange, 17 x 73 mm, notched, see page 994.
Internal latch DK 7824.510, see page 919.

Packs of	Model No. DK
4	7824.500



Lock

for side panel, plug-type

With security lock insert no. 3524 E, in exchange for the existing toggle locks.

Supply includes:

4 locks, 2 keys.

Internal latch

for side panel, plug-type

Additional security is achieved via the option of latching the side panel from the inside.

The side panels on the frame section are screw-fastened from the inside with latching brackets.

Supply includes:

Assembly parts.



For enclosure system	Packs of	Model No. DK	Model No. FR
TS	4	7824.510	–
FR(i)	4	–	7856.700