

Roof/wall mounting

Roof



Roof plates

for SV-TS

For SV-TS 8 enclosures without roof plate and in exchange for the standard roof plate for other TS enclosures.

Material:
Sheet steel, 1.5 mm

Surface finish:
Textured paint

Colour:
RAL 7035

Supply includes:
Mounting accessories.

IP 55, solid

For enclosures		Packs of	Model No. SV
Width mm	Depth mm		
300	600	1	9671.636
400	600	1	9671.646
600	600	1	9671.666
800	600	1	9671.686
300	800	1	9671.638
400	800	1	9671.648
600	800	1	9671.668
800	800	1	9671.688

IP 43 with ventilation hole Build height: 93 mm

For enclosures		Packs of	Model No. SV
Width mm	Depth mm		
300	600	1	9671.736
400	600	1	9671.746
600	600	1	9671.766
800	600	1	9671.786
300	800	1	9671.738
400	800	1	9671.748
600	800	1	9671.768
800	800	1	9671.788

IP 2X with ventilation hole Build height: 72 mm

For enclosures		Packs of	Model No. SV
Width mm	Depth mm		
400	600	1	9671.846
600	600	1	9660.235
800	600	1	9660.245
1000	600	1	9660.255
1200	600	1	9660.265
400	800	1	9671.848
600	800	1	9659.525
800	800	1	9659.535
1000	800	1	9659.545
1200	800	1	9659.555

With pressure relief valve Build height: 25 mm

For enclosures		Packs of	Model No. SV
Width mm	Depth mm		
400	600	1	9671.446
600	600	1	9660.935
800	600	1	9660.945
1000	600	1	9660.955
1200	600	1	9660.965
400	800	1	9671.448
600	800	1	9671.468
800	800	1	9671.488

Extended delivery times.

For cable entry glands

For enclosures		Required number of glands	Packs of	Model No. SV
Width mm	Depth mm			
600	400	2	1	9665.943
850	400	3	1	9665.953
1100	400	4	1	9665.963
300	600	2	1	9671.536
400	600	3	1	9671.546
600	600	4	1	9665.903
800	600	8	1	9671.586
850	600	6	1	9665.913
1100	600	8	1	9665.923
300	800	2	1	9671.538
400	800	4	1	9671.548
600	800	8	1	9671.568
800	800	8	1	9671.588



Also required:

Cable entry gland,
see page 623.