

Roof/wall mounting

Wall mounting

Pole clamp

for KL, EB, BG, AE, KS

For reliable, convenient fastening to round or square poles.

For pole diameter/size:

- Ø from 40 to 190 mm
- □ from 50 to 150 mm

Material:

- Mounting angles, clamping section: Sheet steel
- Clamping strap: Stainless steel 1.4301 (AISI 304)

Surface finish:

- Mounting angle, clamping section: Zinc-plated

Supply includes:

- 2 mounting angles, 600 mm long
- 4 clamping sections
- 2 clamping straps
- 4 clamping brackets
- 4 screws and captive nuts M8 for mounting on the enclosure

Packs of	Model No.
1 set(s)	2584.000



Enclosure connectors

Adjustable

Between Command Panels, terminal boxes, compact enclosures and horizontal or vertical surfaces. Pre-mount the connector halves on both sides, screw together and secure with a locking screw, and/or adjust the angle of rotation.

Rotation range:

- ±105° adjustable in 7.5° stepped increments

Material:

- Die-cast zinc

Surface finish:

- Powder-coated

Colour:

- RAL 7035

Supply includes:

- Assembly parts for both sides.

Packs of	Model No.
1 set(s)	6016.200

Note:

- The locking screws may be exchanged for standard, commercially available clamping levers (M10 x 50 mm)

