

Interior installation

Rail systems

Punched rail 23 x 23 mm

for Flex-Block

Supports tool-free installation in two levels via a plug-in system in the Flex-Block depth. For the installation of cable clamp rails.

Installation options:

- In the width and depth

Material:

- Sheet steel

Surface finish:

- Zinc-plated

Supply includes:

- 12 punched rails
- Assembly parts for mounting

Length mm	For width/depth mm	Packs of	Model No.
245	400	12 pc(s).	4169.500
345	500	12 pc(s).	4170.500
445	600	12 pc(s).	4171.500
645	800	12 pc(s).	4172.500



Accessories:

- Cable clamp rail (4193.000 etc.), see page 665



PS punched section without mounting flange 23 x 73 mm

for TS, SE

Installation options:

- On the vertical enclosure section
 - Directly via support brackets TS
 - Via adaptor rail for PS compatibility in conjunction with support brackets PS
- On the horizontal enclosure section
 - Directly via support brackets PS

Material:

- Sheet steel

Surface finish:

- Zinc-plated

Length mm	For WHD mm	Packs of	Model No.
295	400	4 pc(s).	4374.000
395	500	4 pc(s).	4375.000
495	600	4 pc(s).	4376.000
695	800	4 pc(s).	4377.000
895	1000	4 pc(s).	4382.000
1095	1200	4 pc(s).	4378.000
1695	1800	4 pc(s).	4379.000
1895	2000	4 pc(s).	4380.000
2095	2200	4 pc(s).	4381.000



Also required:

- Support brackets PS/TS, see page 620



Accessories:

- Screws, see page 625
- Cable tie for fast assembly 2597.000, see page 667
- U nuts, see page 624

Configuration examples:

See page 598

