

Hygienic Design system enclosure



Material:

- Stainless steel 1.4301 (AISI 304)
- Enclosure: 1.5 mm
- Door: 2.0 mm
- Lock inserts: Stainless steel
- Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600
- Mounting plate: Sheet steel

Surface finish:

- Brushed, grain 400, $R_a < 0.8 \mu\text{m}$
- Mounting plate: Zinc-plated
- Seal: Blue, dyed (RAL 5010)

Protection category IP to IEC 60 529:

- IP 66

Protection category IP to DIN 40 050-9:

- IP 59 K

Supply includes:

- Enclosure, closed at rear and bottom, open at top and sides
- Door
- Mounting plate

System enclosure HD

Width mm	Packs of	400	600	800	1200	Page
Height mm	1 pc(s).	1800	1800	1800	1800	
Depth mm	1 pc(s).	500	500	500	500	
Model No.	1 pc(s).	4000.485	4000.685	4000.885	4000.285	
Accessories						
HD side panels	1 pair(s)	4000.185	4000.185	4000.185	4000.185	11
HD baying frame	1 pc(s).	4000.785	4000.785	4000.785	4000.785	11
Mounting plate infill	1 pc(s).	4000.508	4000.508	4000.508	4000.508	11
HD angled roof 30°, open at the sides	1 pc(s).	4000.545 ¹⁾	4000.565	4000.585	4000.525 ¹⁾	11
HD side panels for angled roof	1 pair(s)	4000.505	4000.505	4000.505	4000.505	11
Interior installation		see mounting and operating instructions				
HD cable gland		see page 15				
T handles with/without lock cylinder		on request				
HD supporting structure with levelling		on request				

¹⁾ Extended delivery times.

