

Wall-mounted hinge CP 120

Horizontal outlet, without height offset

For swivel mounting of the support arm on vertical surfaces.

Material:

- Wall-mounted hinge: Cast steel
- Concertina section: Plastic

Colour:

- Wall-mounted hinge: RAL 7035
- Concertina section: RAL 7024

Rotation range:

- approx. 180°
- Adjustable to a limited extent by means of 2 slotted steel discs

Supply includes:

- Concertina section
- Screws for restricting rotation range
- Adjusting screws
- Self-tapping screws for support section attachment
- Seals

Further technical information:

Available on the Internet

Rotating/tilting	Packs of	Model No.
■	1 pc(s).	6212.780



Coupling CP 180

for support arm connection Ø 130 mm

For swivel mounting the enclosure on the vertical section of the support arm system CP 180.

Material:

- Die-cast zinc
- Enclosure connection: Cast aluminium

Colour:

- RAL 7035

Rotation range:

- approx. 310°, lockable via clamping levers
- The range of rotation can be limited by inserting the pins provided

Supply includes:

- Pins to limit the rotation range
- Self-tapping screws for support section attachment
- Seals

Further technical information:

Available on the Internet

Weight kg	Rotating/tilting	Packs of	Model No.
5.3	■	1 pc(s).	6218.300



Pivot

with/without jib

For direct, vertically hinged integration into machines and systems.

Applications:

- Enclosure suspended or top-mounted

Benefits:

- With integral rotation range restricter

Installation options:

- To fit enclosures with support arm connection Ø 130 mm

Load capacity:

- 700 N

Rotation range:

- approx. 310°
- The range of rotation can be limited by inserting the grub screws provided

Further technical information:

Available on the Internet

Jib length mm	Colour	Packs of	Model No.
200	RAL 7024/7035	1 pc(s).	6206.850
–	RAL 7035	1 pc(s).	6206.870

