

Side panels

for TE 8000

Simple assembly with insertion aid at the bottom and lock at the top. Earthing bolt with contact lug.

Material:

- Sheet steel

Surface finish:

- Powder-coated

Colour:

- RAL 7035

Protection category IP to IEC 60 529:

- IP 20

Supply includes:

- Side panels, lockable, including security lock 3524 E

For enclosure height mm	For enclosure depth mm	Packs of	Model No.
2000	800	2 pc(s).	7888.652
2000	1000	2 pc(s).	7888.653



Baying kit

for TE/TE

For connecting individual enclosures into bayed suites at the sides. The enclosures are connected between the base and roof frame.

Benefits:

- Baying of TE 8000 to TE 7000 enclosures is supported

Material:

- Sheet steel, spray-finished

Colour:

- RAL 7035

Supply includes:

- Assembly parts

Packs of	Model No.
4 pc(s).	7888.640



Transport castors

for TE

The castors may be screw-fastened in the corner areas within the base frame in place of the levelling feet. Ground clearance: 58 mm, mounting thread M10 x 20.

Supply includes:

- Assembly parts

Max. load capacity (static) per enclosure kg	Packs of	Model No.
300	4 pc(s).	7000.672



Brush kit

for TE 8000

To activate cable entry in the roof plate.

Benefits:

- For simple top-mounting on the cut-out edge

Material:

- Plastic support with brushes

For enclosure width mm	Packs of	Model No.
600	2 pc(s).	7888.610
800	2 pc(s).	7888.612

