

PC enclosure systems



System accessories Page 507 Monitors, keyboards Page 706/707 Climate control Page 307 PC enclosure system, stainless steel Page 187

Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access.

Material:

- Enclosure, door, mounting compartment, supports: Sheet steel
- Handles, decorative trim panels: Plastic
- Door trim panels: Aluminium
- Viewing window: Single-pane safety glass

Surface finish:

- Enclosure and door: Dipcoat-primed, powder-coated on the outside, textured paint
- Mounting compartment, support: Powder-coated

Colour:

- Enclosure, door, decorative trim panels, supports: RAL 7035
- Handle: Similar to RAL 9006
- Monitor field, central door section: RAL 7015

Protection category IP to IEC 60 529:

- IP 55

Protection category NEMA:

- NEMA 12

Supply includes:

- Enclosure, door, rear door
- Please note the product-specific scope of supply.

Approvals:

- UL
- cUL

Technical details:

Available on the Internet

Width mm	Packs of	600	600	600	600	600	600	Page
Height mm		1600	1600	1600	1600	1600	1600	
Depth mm		636	636	636	636	636	836	
Product-specific scope of supply								
Glazed door, top		■	■	■	■	-	■	
Keyboard drawer		■	-	-	■	■	■	
Component shelf		■	■	■	■	-	■	
Folding keyboard		-	■	-	-	-	-	
Desk section		-	-	■	-	-	-	
Mounting compartment, small		-	-	-	■	-	-	
Mounting compartment, large		-	-	-	-	■	-	
Model No.	1 pc(s).	5366.000	5366.100	5366.200	5366.300	5366.400	5368.000	
Max. keyboard dimensions (WxHxD) mm		480 x 70 x 260	475 x 50 x 250 475 x 60 x 200	540 x 40 x 175	480 x 70 x 260	480 x 70 x 260	480 x 70 x 260	
Accessories								
Base/plinth, stationary	1 pc(s).	8800.920	8800.920	8800.920	8800.920	8800.920	-	517
Base/plinth components, front and rear, 100 mm	1 set(s)	8601.600	8601.600	8601.600	8601.600	8601.600	8601.600	513
Base/plinth components, front and rear, 200 mm	1 set(s)	8602.600	8602.600	8602.600	8602.600	8602.600	8602.600	513
Base/plinth trim panels, side, 100 mm	1 set(s)	8601.060	8601.060	8601.060	8601.060	8601.060	8601.080	514
Base/plinth trim panels, side, 200 mm	1 set(s)	8602.060	8602.060	8602.060	8602.060	8602.060	8602.080	514
Partial mounting plates	1 pc(s).	8614.675	8614.675	8614.675	8614.675	8614.675	8614.675	596
Component shelf, pull-out	1 pc(s).	6902.960	6902.960	6902.960	6902.960	6902.960	6902.980	627
Drawer tray	1 pc(s).	6902.700	6902.700	6902.700	6902.700	6902.700	6902.700	628
Paper removal flap	1 pc(s).	6903.200	6903.200	6903.200	6903.200	6903.200	6903.200	713
Socket strips in an aluminium duct		see page	see page	see page	see page	see page	see page	422
Lock systems		from page	from page	from page	from page	from page	from page	562