

## Fibre-optic shunting rings

Fibre-optic shunting or jumper cables can be inserted into the grooves of the inner body. A rubber ring holds different fibre-optic cables with diameters of up to 4.5 mm. Strain relief and bending radius are ensured.

Length: 120 mm

### Material:

- Dual compound plastic

### Colour:

- Exterior: RAL 7035
- Interior: Black

### Supply includes:

- 2 rubber rings
- Baying kit
- Mounting accessories

### Assembly:

The supplied mounting brackets are suitable for universal use; the fibre-optic cables can be routed to the patch panel in all directions in various mounting positions:

- 1 At the side, directly on the patch panel
- 2 In front of the patch panel
- 3 At the side next to the patch panel
- 4 Behind the patch panel

Packs of	Model No.
2 pc(s).	7116.500

### Possible alternative:

- Fibre-optic cable management panel, 1 U, see page 677



## System supports for cable routes

### for TS

The depth-variable support system may be attached to all 800 – 1200 mm deep TS enclosures with external screw-fastening of the roof plate. The integral system punchings, for screws or captive nuts, support the attachment of most common cable route systems.

- May be combined with TS-IT fan mounting plate
- In combination with punched rail, suitable for accommodating additional cable routing rails or pipelines
- Support height: 102 mm

### Material:

- Sheet steel

### Surface finish:

- Powder-coated

### Colour:

- RAL 7035

Packs of	Model No.
2 pc(s).	7831.472

### Accessories:

- Metal multi-tooth screws 5.5 x 13 mm, 2486.500, see page 625
- Captive nuts M6, 8800.340, see page 624

