

Cable management

Cable entry



Section for cable entry, rear for TS, SE, CM, TP

Unlike the section for cable entry, centre, the rear section is mounted directly onto the base opening. In this way, when installing the mounting plate in the rearmost position (TS) or with CM, the cables may be routed directly on a cable clamping rail with no large radii. In conjunction with the cable clamp rail, optimum adjustment between the cable entry and mounting plate can be achieved.

Material:

- Extruded aluminium section
- Seal: PU foam
- Cross-section: 30 x 25 mm

Protection category IP to IEC 60 529:

- IP 55 if installed correctly

Note:

- 1 set is sufficient for one base opening up to an enclosure width of 800 mm. From an enclosure width of 1000 mm, two base openings are provided.
- 2 sets per enclosure may be fitted

For enclosure width mm	Packs of	Model No.
600	1 set(s)	8802.065
800	1 set(s)	8802.085
1000	2 set(s)	8802.105
1200	2 set(s)	8802.125
1600	2 set(s)	8802.165



Accessories:

- Cable clamp rail, see page 665



Foam rubber cable clamp strip

For sealing the cable entry between the gland plates. Particularly suitable for identical cable cross-sections.

Material:

- PU foam
- Cross-section: 30 x 30 mm

Protection category IP to IEC 60 529:

- IP 55 if installed correctly

Packs of	Model No.
3 m	2573.000



EMC gland plates

see page 641