

482.6 mm (19") installation system

Swing frames



Swing frame, small

Installation for TS, SE, 600 mm and 800 mm wide enclosures

For mounting 482.6 mm (19") equipment.

Material:

– Sheet steel

Surface finish:

– Zinc-plated

Supply includes:

– Cam with double-bit lock insert and parts for attaching to the installation kit

Technical details:

Available on the Internet

Installation		Front, top/bottom	Set back, top/bottom	Set back, front, centre
U	Packs of	Model No.		
3	1 pc(s).	2377.030		
6	1 pc(s).	2377.060		
9	1 pc(s).	2377.090		
12	1 pc(s).	2377.120		
15	1 pc(s).	2377.150		
18	1 pc(s).	2377.180		
Also required:				
1 Installation kit		1 set(s)	For enclosure width	
			600	800
			2377.860	2377.880
2 PS punched section without mounting flange Requirements: 2 or 4 pc(s).		For enclosure depth mm		Page
		400	4 pc(s).	4374.000 611
		500	4 pc(s).	4375.000 611
		600	4 pc(s).	4376.000 611
		800	4 pc(s).	4377.000 611
Support bracket, 2 pc(s). required per PS punched section without mounting flange			6 set(s)	8800.330 620
Accessories				
Lock inserts, type D				2484.000 570

Note:

– The swing frame stay is required to hold open the swing frame, see page 681