

482.6 mm (19") installation system

Swing frames

Compact swing frame

for AE

For the installation of slide-in electronic equipment, 482.6 mm (19") across the entire height.

Technical specifications:

– Torsionally stiff frame, welded from rectangular tube and triple-folded support section

Material:

– Sheet steel

Colour:

– RAL 7035

Supply includes:

– Double-bit lock insert and assembly parts

Width mm	600	600	600/760
Height mm	380	600	760
U	6	11	14
Packs of	1 pc(s).	1 pc(s).	1 pc(s).
Model No.	2026.200	2027.200	2034.200



Accessories:

– 41 mm lock insert, type C, see page 570

Technical details:

Available on the Internet



Swing frame stay

Holds the swing frame in the open position.

For mounting on swing frame, large:

- 1979.200, at the top of the enclosure
- 1980.200, at the bottom of the enclosure (with safety catch at 160°)

	Packs of	Model No.
with 130° hinge	5 pc(s).	1979.200
with 180° hinge	1 pc(s).	1980.200

For mounting on swing frame, small:

- 1979.200, may be mounted at the top or bottom on the installation kit



Slide rails

To support heavy slide-in electronic equipment, 482.6 mm (19") in the swing frame.

Material:

– Sheet steel

Surface finish:

– Zinc-plated

For equipment with a max. installation depth	Packs of	Model No.
D max. < 190 mm	10 pc(s).	1962.200
D max. > 190 mm	10 pc(s).	1963.200

