

### Busbars E-Cu

#### with integral holes

Suitable for

- Direct installation in enclosures
- Busbar support
  - SV 9340.000/.010, see page 276
  - SV 9340.004, see page 276
  - SV 9342.014, see page 276
  - SV 3052.000, see page 340
  - SV 3073.000, see page 340
- PE/PEN combinations in conjunction with PE/PEN combination angles, see page 694 and baying bracket E-Cu, see page 694.

#### Detailed drawings:

Available on the Internet.



Size 30 x 5 mm (hole Ø 11 mm)				
For enclosure width mm	Length mm	Packs of	Model No. SV	Page
300	265	2	<b>9661.335</b>	
400	365	2	<b>9661.345</b>	
600	565	2	<b>9661.365</b>	
800	765	2	<b>9661.385</b>	
1000	965	2	<b>9661.305</b>	
1200	1165	2	<b>9661.325</b>	
Accessories				
Baying bracket E-Cu	95	4	9661.355	694
PE/PEN combination angle	–	4	9661.235	694

Size 30 x 10 mm (hole Ø 11 mm)				
For enclosure width mm	Length mm	Packs of	Model No. SV	Page
300	265	2	<b>9661.330</b>	
400	365	2	<b>9661.340</b>	
600	565	2	<b>9661.360</b>	
800	765	2	<b>9661.380</b>	
1000	965	2	<b>9661.300</b>	
1200	1165	2	<b>9661.320</b>	
Accessories				
Baying bracket E-Cu	95	4	9661.350	694
PE/PEN combination angle	–	4	9661.230	694

Size 40 x 10 mm (hole Ø 14 mm)				
For enclosure width mm	Length mm	Packs of	Model No. SV	Page
300	292	2	<b>9661.030</b>	
400	392	2	<b>9661.040</b>	
600	592	2	<b>9661.060</b>	
800	792	2	<b>9661.080</b>	
1000	992	2	<b>9661.000</b>	
1200	1192	2	<b>9661.020</b>	
Accessories				
Baying bracket E-Cu	88	4	9661.350	694
PE/PEN combination angles for use with Form 2-4	–	4	9661.240	694
PE/PEN combination angles for other applications	–	4	9661.200	694

Size 80 x 10 mm (hole Ø 14 mm)				
For enclosure width mm	Length mm	Packs of	Model No. SV	Page
300	292	2	<b>9661.130</b>	
400	392	2	<b>9661.140</b>	
600	592	2	<b>9661.160</b>	
800	792	2	<b>9661.180</b>	
1000	992	2	<b>9661.100</b>	
1200	1192	2	<b>9661.120</b>	
Accessories				
Baying bracket E-Cu	88	4	9661.150	694
PE/PEN combination angles for use with Form 2-4	–	4	9661.240	694
PE/PEN combination angles for other applications	–	4	9661.200	694