

Interior installation

Mounting plates

Mounting plate attachment

For additional clamping and to reduce potential vibration of the mounting plate. Select according to mounting position, installation type and enclosure.

Material:

- Sheet steel

Surface finish:

- Zinc-plated

Supply includes:

- Assembly parts

For TS, SE

Installation options:

- All-round
- Set forward on a 25 mm pitch pattern

Slide in between the bar and plate from below or above or from the side, and secure with screws.

Packs of	Model No.
10 pc(s).	4593.000

**Also required:**

- Support strip (with TS for inner level), see page 609 or
- Punched section with mounting flange (with TS for inner level), see page 606 or
- Punched rails and punched sections, see page 610/611

For TS, SE

Installation options:

- On the top and bottom of the mounting plate
- Rear, flush with enclosure frame

Screw in the clip behind the plate and secure with screws.

Packs of	Model No.
10 pc(s).	4576.000

Installation kit

for mounting plates TS, SE, back-to-back

The minimal distance between the two mounting plates ensures a maximum installation depth for installed equipment on both sides.

Material:

- Sheet steel

Surface finish:

- Zinc-plated

Note:

Build height front and rear, with central installation = (enclosure depth - 48 mm) : 2

Example:

8806.521 = Depth 600 mm

Build depth = 2 x 276 mm

Packs of	Model No.
1 set(s)	8800.280

