


TopTherm wall-mounted cooling units "Blue e"

Output class 750 W

Model No.	Packs of	3361.500	3361.510	3361.540	3361.600	Page
Material	Sheet steel	■	■	■	–	
	Stainless steel	–	–	–	■	
Colour	RAL 7035	■	■	■	–	
Total cooling output 50 Hz L35 L35 to DIN EN 14511 kW		0.85	–	0.85	0.85	
Total cooling output 50/60 Hz L35 L35 kW		0.85 / 0.89	0.89	0.85 / 0.89	0.85 / 0.89	
Total cooling output 50/60 Hz L35 L50 kW		0.67 / 0.67	0.67	0.67 / 0.67	0.67 / 0.67	
Rated operating voltage V, ~, Hz		230, 1~, 50/60	115, 1~, 60	400, 2~, 50/60	230, 1~, 50/60	
Width (B) mm		280	280	280	280	
Height (H) mm		550	550	550	550	
Depth (T) mm		280	280	280	280	
Rated current max. A		2.7 / 2.7	5.3	1.2 / 1.4	2.7 / 2.7	
Start-up current A		6 / 9.6	12	3.1 / 3.3	6 / 9.6	
Pre-fuse A		10	10	–	10	
Transformer circuit-breaker A		–	–	6.3...10	–	
Toroidal transformer (external) Ø x D mm		–	–	126 x 65	–	
Power consumption P _{el} 50/60 Hz L35 L35 kW		0.41 / 0.44	0.56	0.41 / 0.44	0.41 / 0.44	
Power consumption P _{el} 50/60 Hz L35 L50 kW		0.47 / 0.5	0.66	0.47 / 0.5	0.47 / 0.5	
Operating temperature range		+10°C...+55°C	+10°C...+55°C	+10°C...+55°C	+10°C...+55°C	
Operating temperature (max.) 60 Hz		+10°C...+53°C	+10°C...+52°C	+10°C...+53°C	+10°C...+53°C	
Setting range		+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	
Energy efficiency ratio (EER) 50 Hz L35 L35 to DIN EN 14511		2.08	1.59	2.08	2.08	
Refrigerant g		R134a, 280	R134a, 260	R134a, 280	R134a, 280	
Permissible operating pressure (p. max.) bar		28	28	28	28	
Air throughput of fans (unimpeded air flow), internal circuit / external circuit m³/h		230 / 550	230 / 625	230 / 550	230 / 550	
Weight kg		22.0	22.0	22.0	22.0	
Accessories						
Filter mats	3 pc(s).	3286.300	3286.300	3286.300	3286.300	369
Metal filters	1 pc(s).	3286.310	3286.310	3286.310	3286.310	370
Door-operated switch	1 pc(s).	4127.010	4127.010	4127.010	4127.010	639
Condensate hose	1 pc(s).	3301.610	3301.610	3301.610	3301.610	377

Accessories



Thermoelectric coolers

see page 334